

# SUPAPORE NANOFIBRE

## Positive Charged Nanofibre Filters



Amazon Filters' **SupaPore NanoFibre** filters contain a pleated filter media that exhibits a very high level of positive charge. This provides a cartridge that offers both high flow and efficient removal of ultrafine contaminants. The heart of the filter is a nanoalumina and glass microfibre media that delivers >50 millivolts Zeta potential at pH 7.2. This construction also produces a filter media with a very high internal surface area - a sheet of media of 1m<sup>2</sup> has approximately 42,000 m<sup>2</sup> internal surface area. Therefore **SupaPore NanoFibre** filters are a very cost effective method for removing negatively-charged contaminants from aqueous solutions and polar solvents.

### Typical Applications

**SupaPore NanoFibre** filters are an alternative to the use of ultrafiltration or very fine sub-micron membrane filters for many applications. The media has passed USP Class VI Plastics testing and meets NSF standards 42 and 53 for potable water, so can be used in both critical and industrial applications. The high level of positive charge allows the use of a relatively open porous structure, providing much higher flow rates when compared to existing technology.

Typical applications include :-

- Removal of endotoxins from purified water and pharmaceutical processes\*<sup>1</sup>
- Bacterial bioburden reduction and virus removal
- Purification of drinking water
- Protection of RO membranes from premature fouling by colloids, organic material, particulates etc
- Activated carbon capture
- Reduction in levels of heavy metals from waste streams e.g. in plating facilities
- Dissolved trace oil removal
- Rouge removal in boiler/heat exchanger applications



## Features and Benefits

- Relatively open porous structure offering high flow rates and long in-process life times
- High Zeta potential for effective removal of ultrafine contaminants
- Enormous internal surface area providing high capacity for contaminant removal
- Media tested to ensure suitability for critical processes including pharmaceutical applications and potable water
- Product Validation Guide available
- All individual packing bags are anti static

\* Not recommended for dialysis applications

## Industries and Applications

- |                                 |   |  |
|---------------------------------|---|--|
| <b>Water Treatment</b>          | • | Removal of endotoxins from purified water, RO protection |
| <b>Pharmaceutical processes</b> | • | Bioburden and endotoxin reduction                        |
| <b>Potable water</b>            | • | Removal of contaminants                                  |
| <b>Waste water treatment</b>    | • | Removal of heavy metals, emulsions                       |

**AMAZON**

# SupaPore Nanofibre Technical Data

## Dimensions

Outside diameter: 68.5mm  
 Typical surface area: 0.22m<sup>2</sup> per 10" filter

## Sterilisation and Sanitisation<sup>2</sup>

Steam or Autoclave: 121°C for 15 mins (40 cycles)  
 Hot Water: 90°C for 30 mins (0.2 bar Δp max)  
<sup>2</sup> Applies to single open end cartridges only. For all steaming and hot water applications, the Reinforced Polypropylene End Cap option must be used.


## Maximum Operating Conditions

Temperature: 80°C  
 Recommended Maximum Differential Pressure:  
 Forward Flow: 4.0 Bar @ 20°C  
 Reverse Flow: 3.5 Bar @ 20°C  
 Recommended change-out differential pressure: 2.5 Bar

## Standard Materials of Construction

Filter Media: Borosilicate Glass Microfibre and Nanoalumina  
 Media support: Polypropylene  
 End Caps: Polypropylene  
 Cage/Core: Polypropylene

Product validation guide available on request. All SupaPore Nanofibre cartridges are manufactured under strict control with batch number identification, giving full traceability on all components.



## Ordering Guide

16A	DG	002 -	09	0	E	A	
Media	Core/Assembly	Micron Rating	Length	End Caps	Seal	Branding	Options
A - Nanofibre / Polypropylene	DG - Polypropylene Cage and End Caps, Reinforced Polypropylene Core PG - Polypropylene	002 - 0.2µm	09 - 250mm 20 - 509 30 - 762 40 - 1016	0 - DOE A - Code A B - Code B <sup>*3</sup> S - Code S 2 - Code 2 3 - Code 3 6 - Code 6 7 - Code 7 8 - Code 8 9 - Code 9 J - Junior	B - Buna E - EPDM F - FEP / Silicone S - Silicone V - Viton	A - Amazon P - Plain	G - Reinforced Polypropylene End Cap A - Millidisk Retrofit <sup>*4</sup> B - 1/2" BSPM Thread Retrofit <sup>*4</sup> C - Truseal Retrofit <sup>*4</sup>

Example: 16APG002-303SA = Nanofibre media with polypropylene core, General Grade, 0.2µm, triple length 30" long, Code 3 end fitting with Silicone seal.  
<sup>\*3</sup> - Code B to fit Amazon 50 Series housings only  
<sup>\*4</sup> - Juniors only. Reinforced Polypropylene End Cap as standard

# AMAZON FILTERS LTD.

Albany Park Estate, Camberley, Surrey, GU16 7PG, ENGLAND

Tel: +44 (0) 1276 670 600 Email: sales@amazonfilters.co.uk Web: www.amazonfilters.com

SupaPore is a trademark of Amazon Filters Ltd.

AMAZON FILTERS LTD. reserve the right to change specification without prior notice, as part of their continuous product development programme.

16AP - Issue 04